

## Augen HD Single Vision Lenses®

### Availability

Aspheric = A  
Double Aspheric = AA

Trivex® Hard Coated

	BASE							74 mm
	0.75	2.00	3.50	4.00	5.00	6.25	7.25	8.25
A								
AA								

Trivex Transitions® Hard Coated

	BASE							74 mm
	0.75	2.00	3.50	4.00	5.00	6.25	7.25	8.25
A								
AA								

### NEW!

AugenSOL™ 1.50 Photochromic Hard Coated

	BASE							71 mm
	0.75	2.00	3.50	4.00	5.00	6.25	7.25	8.25
A								
AA								

Hard Resin 1.50 Uncoated

	BASE							74 mm
	0.75	2.00	3.50	4.00	5.00	6.25	7.25	8.25
A								
AA								

1.56 Index Hard Coated

	BASE							71 mm
	0.50	2.00	3.00	4.00	5.00	6.00	7.50	8.50
A								



Available through:

# SINGULAR PERFORMANCE

Augen HD Single Vision Lenses  
Wide, Clear, Natural Vision



## AUGEN FREE FORM INSIDE

All Augen HD premium lenses are created from molds produced with our proprietary free-form process, resulting in precision lens products that deliver the exact characteristics intended by our design team.

You can prescribe with complete confidence, knowing every lens meets our highest criteria for sharp, clear vision regardless of prescription.



HIGH DEFINITION LENSES®

866.284-3611  
augenoptics.com

©2011. All rights reserved. Augen High Definition Lenses is a registered trademark and AugenSOL is a trademark of Augen Optics. Trivex is a registered trademark of PPG Industries. Transitions is a registered trademark of Transitions Optical, Inc. OMK1069.02

augenoptics.com




## A New Approach to Aspheric Design

The advanced, patented aspheric design of Augen HD Single Vision Lenses extends the benefits of asphericity to low and medium prescriptions while enhancing higher prescriptions. So every wearer sees with impressive clarity in all viewing directions, even hard-to-fill high cylinder Rx's.

- Aspheric lens is aspherized for cylinder power for Rx's with low or no cylinder (up to -0.50D cyl)
- Double Aspheric lens is aspherized for both cylinder and sphere power for Rx's with high cylinder (from -0.75D cyl)
- Appropriate lens choice is determined by the Rx, so there's no need to specify
- Unique design provides flatter curves for all Rx's

Aspherized for Cylinder power

Aspherized for Sphere power




## Wider Fields of Natural Vision




### Conventional Lens

Conventional lenses provide clear vision in the central area of the lens only.



### Augen HD Aspheric Lens

Augen HD Aspheric Single Vision Lenses gradually flatten towards the edges of the lens, eliminating distortion and providing a wide field of natural vision.



### Augen HD Double Aspheric Lens

Augen's patented HD Double Aspheric Single Vision Lens allows you to provide wide, clear vision even for hard-to-fill high cylinder prescriptions.

## NEW! Available in AugenSOL™ Photochromic

Augen HD Single Vision Lenses are available in new AugenSOL™ Photochromic, the most advanced photochromic hard resin material available today.

- Gets dark exceptionally fast outdoors - nearly sun lens dark in just 12 seconds
- Provides 100% UVA/UVB protection on both front and back lens surfaces
- Extra-dark tint rivals the light protection offered by sun lenses
- Fades quickly to barely noticeable tint indoors for clear, translucent lenses



AUGENSOL™  
PHOTOCHROMIC LENS